

PLC-BSC- 60DC/21

Order No.: 2966100



6.2 mm PLC basic terminal blocks with screw connection method, input voltage 60 V DC (without relay or optocoupler)

| Commercial data | |
|-----------------|---------------|
| EAN | 4017918162030 |
| Pack | 10 pcs. |
| Customs tariff | 85364190 |
| Weight/Piece | 0.03047 KG |

Product notes

WEEE/RoHS-compliant since: 04/05/2007



<http://www.download.phoenixcontact.com>
Please note that the data given here has been taken from the online catalog. For comprehensive information and data, please refer to the user documentation. The General Terms and Conditions of Use apply to Internet downloads.

Technical data

| Input data | |
|-----------------------------|--|
| Nominal input voltage U_N | 60 V AC/DC |
| Status display | LED |
| Protective circuitry | Damping diode, polarity protection diode |

Connection data

| | |
|--|----------------------|
| Conductor cross section solid min. | 0.14 mm ² |
| Conductor cross section solid max. | 2.5 mm ² |
| Conductor cross section stranded min. | 0.14 mm ² |
| Conductor cross section stranded max. | 2.5 mm ² |
| Conductor cross section AWG/kcmil min. | 26 |
| Conductor cross section AWG/kcmil max | 14 |
| Type of connection | Screw connection |
| Stripping length | 8 mm |
| Screw thread | M3 |

General data

| | |
|---|---------------------------|
| Width | 6.2 mm |
| Height | 94 mm |
| Depth | 80 mm |
| Color | green |
| Ambient temperature (operation) | -25 °C ... 60 °C |
| Ambient temperature (storage/transport) | -40 °C ... 85 °C |
| Operating mode | 100% operating factor |
| Inflammability class acc. to UL 94 | V0 |
| Mounting position | Any |
| Assembly instructions | In rows with zero spacing |

Certificates / Approvals

Certification

CUL, CUL Listed, GL, GOST, UL, UL Listed, VDE-PZI

Address

PHOENIX CONTACT Inc., USA
586 Fulling Mill Road
Middletown, PA 17057, USA
Phone (800) 888-7388
Fax (717) 944-1625
<http://www.phoenixcon.com>



© 2009 Phoenix Contact
Technical modifications reserved;