

Datasheet

RS Pro Feed Through Terminal Block, CTS series, 2.5mm², 1000 V, 24A, Screw Clamp Termination, White, Single Level

RS Stock No: **796-1038**



Product Details

RS Pro feed through terminal block in white colour, has 1000 V voltage rating and 24 A current rating. This single level, screw clamp termination system has marker holding recesses to accept marking tags for circuit identification and is suitable for 2.5 mm² wires. This block makes cross connection easy with the aid of shorting links/sleeves and screws. It is suitable for control, automation, instrumentation and power distribution applications.

Features and Benefits

- Rated voltage 1000 V
- Marker holding recesses to accept marking tags for circuit identification
- Wire entry orientation side entry
- Suitable for control, automation, instrumentation and power distribution applications

**Specifications:**

Cable CSA	2.5 mm ²
Colour	White
Current Rating	24 A
Maximum Operating Temperature	+85°C
Minimum Operating Temperature	-40°C
Number of Levels	Single
Termination Method	Screw Clamp
Voltage Rating	1000 V
Wire Size	22 to 12 AWG
Dimensions	43 x 5 mm
Material	Polyamide Housing
Screw Size	M2.5
Standards Met	CE, CSA US, IEC