

Decorative Vintage ST64

Decorative Vintage ST64 60W 230/240V B22 SV1

0023866



Range Features

-

PRODUCT OVERVIEW

Lamp finish	Coloured
Colour temperature (K)	1900
CRI (Ra)	100
Dimmable	Yes
EAN code	5410288238661
Energy class	E
Cap/Base	B22
Watt (Nominal) (W)	60
Ordering number	0023866
Average life (Rated) (h)	2000
Luminous flux (Rated) (lm)	150
Technology	Incandescent
Voltage (V)	230-240

DATA TABLE

General data

Average life (Nominal) (h)	2000
Control gear required	No
Lamp finish	Coloured
Dimmable	Yes
EAN code	5410288238661
Energy class	E
Energy saving lamp	No
General application	Hospitality
Intended purpose	Decor Lighting
Cap/Base	B22
Lamp mercury content (mg)	0
Ordering number	0023866
Product name	Decorative Vintage ST64 60W 230/240V B22 SV1

Decorative Vintage ST64

Decorative Vintage ST64 60W 230/240V B22 SV1

0023866

Average life (Rated) (h)	2000
Special purpose lamp	Yes
Starting time (max) (s)	0.01
Technology	Incandescent
Transformer required	No
Warm-up time to 60% of full light (max) (s)	Instant full light

Optical data

Colour temperature (K)	1900
CRI (Ra)	100
Luminous flux (Nominal) (lm)	150
Luminous flux (Rated) (lm)	150
Suitable for accent lighting	No

Electrical data

kWh per 1000 hours burning time	60
Lamp power factor	1
Watt (Nominal) (W)	60
Watt (Rated) (W)	60
Voltage (V)	230-240

Physical data

Max. Lamp Diameter (mm) - D	64
Lamp Length (mm) - C/L	140

Decorative Vintage ST64

Decorative Vintage ST64 60W 230/240V B22 SV1

0023866

