



SEZ. A-A
(SECT. A-A)



1 NORYL, UL94 V1, COLORE NERO

2 NORYL SE-1 COLORE ROSSO

3 TOLLERANZA NON CUMULATIVA

1 NORYL, UL94 V1, BLACK COLOUR


2 NORYL SE-1 RED COLOUR

3 NON CUMULATIVE TOLERANCE

SCALA NON IMPEGNATIVA
(DO NOT SCALE)
DIMENSIONI IN mm
(DIMENSIONS IN mm)

METRIC

PROIEZIONE EUROPEA
(EUROPEAN PROJECTION)



4	1-280359-0	7.62	10.6	12.2	2
2	1-280358-0	2.54	5.6	7.1	
22	280364-0	53.34	56.4	57.9	1
15	280363-0	35.56	38.6	40.1	
12	280514-0	27.94	31	32.5	
10	280362-0	22.86	25.9	27.4	
9	280512-0	20.32	23.3	24.9	
8	280361-0	17.78	20.8	22.3	
6	280360-0	12.70	15.7	17.3	1
4	280359-0	7.62	10.6	12.2	
2	280358-0	2.54	5.6	7.1	
N° POS.	PART NUMBER	DIM. "A"	DIM. "B"	DIM. "C"	MATERIAL (SEE NOTE)

CUSTOMER DRAWING
FOR REFERENCE ONLY

DISEGNO PER CLIENTE
SOLO PER RIFERIMENTO

THIS DRAWING IS UNPUBLISHED RELEASE FOR PUBLICATION

TOLLERANZE, SE NON
DIVERSAMENTE SPECIFICATO
(TOLERANCES, UNLESS
OTHERWISE SPECIFIED)

DIAM. ISOLANTE
(INS. DIA. RANGE)

RANGO FILO
(WIRE RANGE)

SCALA
(SCALE)

± 0.3

ANGOLI
(ANGLES)

± 2°

DIS. 11 APRIL '95
(DR.) C.PIA

CONT. 11 APRIL '95
(CHK) R.CANTORE

DESCRIZIONE
(DESCRIPTION) AMPMODU II REC. HSG
SINGLE ROW, CRIMP ON-SNAP IN

LOC. SIZE NUMERO
(DWS NO)

I A3 C-280358

REV.

Y2

FOGLIO
(SHEET)

1 DI 1
(OF)

Y2	REVISED PER ECO-11-005140	RK	30MAR11
REV.	REVISIONI (REVISION RECORD)	DIS. DATA (DR) (DATE)	APP. DATA (APP.) (DATE)