

4

3

2

1

THIS DRAWING IS UNPUBLISHED.

RELEASED FOR PUBLICATION

© COPYRIGHT

ALL RIGHTS RESERVED.

LOC

DIST

REVISIONS

P

LTR

DESCRIPTION

DATE

DWN

APVD





B1

REVISED PER ECO-11-005294

12APR11

RK

HMR




SECT. A-A

NOTE

1. GENERAL TOLERANCE: ± 0.2

② ⚠ ACCEPTABLE OPTION FIGURE BY MANUFACTURING PROCESS
BUT MUST BE NO PROBLEM IN FUNCTION

P/N	MATERIAL	COLOR	HARDNESS	INSULATION DIA
368120-1	SILOPLEN (SILICONE)	BLACK	50-58°	1.8 - 2.6 mm
368120-2	SILOPLEN (SILICONE)	GRAY	50-58°	1.8 - 2.6 mm
388120-4	SILOPLEN (SILICONE)	GREEN	50-58°	1.8 - 2.6 mm

DIMENSIONS:
MM

3rd ANGLE PROJECTION

MATERIAL

SEE TABLE

TOLERANCES UNLESS
OTHERWISE SPECIFIED:

0<XX<10 ±0.2
10<XX<30 ±0.25
30<XX<100 ±0.3
ANGLES ±3°

FINISH

DWN

CHK

APVD

PRODUCT SPEC

APPLICATION SPEC

WEIGHT

0.08 g



TE Connectivity

NAME

NEW RUBBER SEAL (EJ MK-II(+))

SIZE

CAGE CODE

DRAWING NO

A3

00779

C=

3 6 8 1 2 0

SCALE N/S

SHEET

1

OF 1

REV

B1