


NO.	PART NO.	L
1.	YH57-08-01017-323202	1017(40.039)
2.	YH57-08-00317-323202	317(12.48)



1.0 ELECTRICAL

- 1.1 FREQUENCY RANGE: DC-3 GHz
- 1.2 NOMINAL IMPEDANCE: 50 OHM
- 1.3 VOLTAGE RATING: 335 VOLTS MAX.

2.0 MATERIALS

- 2.1 BODIES: BRASS PER JIS-C3604
- 2.2 CENTER CONTACT: BRASS PER JIS-C3604
- 2.3 INSULATION: TEFLON PER ASTM D1457 AND ASTM D1710

3.0 FINISHES AND OTHERS

- 3.1 SEE BELOW TABLE FOR DETAILS.

4.0 MECHANICAL

- 4.1 INTERFACE IN ACCORDANCE WITH: MIL-STD-348A
- 4.2 CABLE RETENTION 15 lbs MIN.

5.0 ENVIRONMENTAL

- 5.1 OPERATING TEMPERATURE RANGE: -40° C TO +85° C

4	19-02-3 174U (50Ω)	1	T.G.G
3	CABLE	1	RG-174/U
2	HEAT-SHRINK TUBE	2	BLACK
1	19-03-3 174U (50Ω)	1	T.G.G
NO	DESCRIPTION	Q'TY	FINISH



APPROVED by _____ DATE: _____

DESCRIPTION		SMA ST. PLUG + SMA R/A PLUG + RG174/U					
製圖	DRAWN	TOLERANCE	品名	YH57-08	DATE	版次	REV.
	<i>Kristina</i>						
檢圖	CHECK	TOLERANCE	單位	mm(in)	DWG.NO.	99-0080	
	<i>Arc</i>						
認定	APPROVAL	.XXX	±0.05	比例	2:1		
	<i>Jenny</i>	ANGLE	±5°				