

Datasheet

## RS Pro HSS 5 to 13; 8 to 20 6 Piece Hex bit Drill Set

RS Stock No: 424-245



### Product Details

RS Pro hex bit drill set consists of six different drill bits of thread size ranging from 5 to 13 mm to 8 to 20 mm. Each precision ground drill bit has HSS construction for the toughest applications. This set contains one of each three-flute 16.5 mm countersink bit, five-flute 15.3 mm countersink bit, 3 to 14 mm deburring bit, 5 to 13 mm cone cut bit, 5 to 13 mm step drill bit and 8 to 20 mm step drill bit.

### Features and Benefits

- Precision ground, HSS power tool accessories with 1/4 Inch hexagon shanks
- Excellent non-slip characteristics when used in 3-jaw chucks
- Set contains one of each three-flute 16.5 mm countersink; five-flute 15.3 mm countersink, 3 to 14 mm deburr, 5 to 13 mm cone cut, 5 to 13 mm step drill and 8 to 20 mm step drill
- Supplied in a wooden box



ENGLISH

### Specifications:

Material	HSS
Maximum Size	8 to 20 mm
Minimum Size	5 to 13 mm
Number of Pieces	6
Set Contents	Countersink Bit; Deburring Tool; Step Drill Bits
Set Type	Hexbit Drill Set