

Cam rollers



Dimensions			Basic load ratings		Fatigue load limit	Maximum radial loads		Limiting speed	Mass	Designation
D	d	B	dynamic C	static C ₀	P _u	dynamic F _r	static F _{0r}			
mm			kN		kN	kN		r/min	kg	-
62	25	20,6	19,9	12,2	0,52	15,3	22	6000	0,32	305805 C-2Z

