

Desktop Labelling machine complete with Carry Case



Ideal for all your office labelling needs, this feature-packed labeller can print a huge range of labels in different sizes. You can create your own styles or use one of the 55 pre-made designs in 18 languages with the Label Collection (or download even more), and to really speed things up it even remembers words you've typed before – perfect for organising even the busiest office!

Key Features

- Save time up to 10mm per second
- 3.5, 6, 9, 12, 18 & 24mm wide durable labels available
- Standalone and PC Connectable
- Convenient built-in automatic cutter
- Easy to use QWERTY keyboard
- Easy-to-read graphical LCD screen
- Includes 24mm black on white tape (4m), AC Adapter and carry case.

Supplies

3.5 mm	6 mm	9 mm	12 mm	18 mm	24 mm
Standard Laminated - 8m					
	TZe-111	TZe-121	TZe-131	TZe-141	TZe-151
			TZe-132		
			TZe-133		
			TZe-135	TZe-145	
	TZe-211	TZe-221	TZe-231	TZe-241	TZe-251
			TZe-231S*		
		TZe-222	TZe-232	TZe-242	TZe-252
		TZe-223	TZe-233	TZe-243	TZe-253
			TZe-334	TZe-344	TZe-354
	TZe-315	TZe-325	TZe-335	TZe-345	TZe-355
		TZe-421	TZe-431	TZe-441	TZe-451
			TZe-431S*		
			TZe-435		
			TZe-531	TZe-541	TZe-551
		TZe-521	TZe-535		TZe-555
	TZe-611	TZe-621	TZe-631	TZe-641	TZe-651
		TZe-721	TZe-731	TZe-741	TZe-751
Fluorescent Laminated - 5m					
			TZe-B31		TZe-B51
			TZe-C31		TZe-C51
Matt Laminated - 8m					
			TZe-M31		
			TZe-MQ135**		
			TZe-MQP35**		
			TZe-MQG35**		
Metallic Laminated - 8m					
			TZe-M931		TZe-M951
Non-Laminated - 8m					
	TZe-N201		TZe-N221	TZe-N231	TZe-N241
					TZe-N251
Flexible ID Laminated - 8m					
	TZe-FX211	TZe-FX221	TZe-FX231	TZe-FX241	TZe-FX251
	TZe-FX611	TZe-FX621	TZe-FX631	TZe-FX641	TZe-FX651
Strong Adhesive Laminated - 8m					
		TZe-S121	TZe-S131	TZe-S141	TZe-S151
	TZe-S211	TZe-S221	TZe-S231	TZe-S241	TZe-S251
		TZe-S621	TZe-S631	TZe-S641	TZe-S651
Fabric - 3m					
			TZe-FA3	TZe-FA4B	
Security Laminated - 8m					
				TZe-SE4	

Optional Extras

-

Product Specifications

Housing Colour	Black and White
Key Board	QWERTY
Number of Keys	
Cutter	Yes (automatic)
Power	AAA x 8pcs or AC adapter (AD-24ES)
LCD	16 chrs x 3 line
Print Method	Thermal
Print Head	180dpi/ 64 dots
Print Speed	10 mm / sec
Tape Type	TZe
Tape Width	Max. Label width 24mm
Max. Print Width	18mm
Number of Characters	462
Number of Symbols	253
Character Sizes	40 (5 widths x 8 Heights)
Fonts	8 (Helsinki, Brussels, US, Los Angeles, San Diego, Florida, Calgary, Belgium)
Font Styles	10 (Normal, Bold, Outline, Shadow, Italic, Italic Bold, Italic Outline, Italic Shadow, Vertical, Solid)
Frames	20 kinds
Underline	Yes
Strikeout	Yes
Multi-Line	7 Lines
Multi-Block	Yes (Max 5 blocks)
Horizontal Alignment	Left (Centre, Right and Just)
Vertical Alignment	No
Cable Labelling	No
Tape Length Setting	Yes (30-300mm)
Tape Margin Setting	None, Narrow, Half, Full, Chain Print
Pre made Designs	55 kinds
Memory	2800 characters 99 areas
Barcodes	Yes (9 kinds)
Time and Date function	Yes
Numbering	Yes (1-9)
Mirror Printing	Yes
Vertical Printing	Yes (in style settings)
Repeat printing	Yes
Print Preview	Yes
Unit	Yes (inch/mm)
Language Change	19 kinds (English, German, French, Spanish, Portuguese, Italian, Dutch, Danish, Norwegian, Swedish, Finnish, Hungarian, Czech, Polish, Romanian, Slovene, Slovak, Croatian, Turkish)

Weights/ Dimensions/ Measures

Dimensions

177mm x 238mm x 70mm

Weight

880g

What's in the box

24mm Black on White Laminated tape (4M)

AD-24ES AC Adapter

Carry Case

Users Guide

Warranty Card

Tape catalogue