






| LOC | DTST | REVISIONS |     |                           |  | DATE    | OWN | APVD |
|-----|------|-----------|-----|---------------------------|--|---------|-----|------|
| J   | ---  | P         | LTR | DESCRIPTION               |  |         |     |      |
|     |      | E2        |     | REVISED PER ECO-11-005030 |  | 23MAR11 | RK  | HMR  |



断面 "B" - "B"  
(SECT)



断面 "C" - "C"  
(SECT)

注;  
1. 通用ハウジング型番 172076, 177627

NOTES,  
1. APPLICABLE H5G 172076, 177627

2. OBSOLETE PARTS: OBSOLETE CIS STREAMLINING PER D.RENAUD/D.SINISI

|             |                          |                      |                                 |             |
|-------------|--------------------------|----------------------|---------------------------------|-------------|
| 2. OBSOLETE | (BRL TYPE)<br>バレルタイプ "E" | ---                  | ↑                               | 170328-2    |
|             | (BRL TYPE)<br>バレルタイプ "D" | 170334-1             | (PRE-TIN BRASS)<br>錫めつき付黄銅 0.4t | 170328-1    |
|             | (REMARKS)<br>備考          | (L/P P/N)<br>ばら状端子型番 | (MATERIAL)<br>材料                | (P/N)<br>型番 |

WIRE RANGE 0.76~2.09mm<sup>2</sup> INSULATION DIA 2.2~3.4mm  
 抱合電線断面積 (AWG #18-#14) 被覆外径

MATERIAL SEE TABLE 表参照 FINISH 仕上

**TE** TE Connectivity

NAME "250" SERIES POSITIVE LOCK (MK- II) REC.  
 "250" シリーズ ポジティブ ロック (マーク II) リセブタクル

| SIZE | CAGE CODE | DRAWING NO | RESTRICTED TO |
|------|-----------|------------|---------------|
| A4   | 00779     | C-170328   | -             |

CUSTOMER DRAWING SCALE 4-1 SHEET 1 OF 1 REV E2

DIMENSIONS,  
単位 mm

TOLERANCES UNLESS  
OTHERWISE SPECIFIED,

一般公差  
10mm : ±0.2  
30mm : ±0.25  
100mm : ±0.3  
ANGLE : ±0.3°

