



2DM1



Actual product appearance may vary.

Snap-in Panel Mount Switch, Double Pole Double Throw (DPDT) Circuitry, 10 A at 277 Vac, Bullet Nose Plunger Actuator, Silver Contacts, Quick Connect Termination

Features

- Attractive, rugged snap-in panel mount design - easy installation
- Choice of momentary, alternate push-pull or pull-to-cheat operation
- Quick-connect terminals
- Expected mechanical life: 1 million operations, 95% survival
- UL recognized file #E22779, CSA certified file #LR4442

Potential

Applications

- Appliance door lights
- Door interlocks
- Stop/start switches

Description

The MICRO SWITCH™ DM/DP Series are snap-action switches in basic and manual configurations. They have quick-connect terminals and snap-in, panel mount housings for ease of installation. They include momentary and alternate actions, and single- or double-pole. The DM accept a button for manual operation. The DP have plungers for basic operation.

Product Specifications	
Switch Type	Snap-in Panel Mount (0.55 in x 1.45 in panel cutout)
Sealed	No
Ampere Rating	10 A
Circuitry	Double Pole Double Throw (DPDT)
Actuator	Bullet Nose Plunger
Termination	Quick Connect
Operating Temperature Range	-37 °C to 82 °C [-35 °F to 180 °F]
Voltage	277 Vac
Approvals	CSA,UL
Contact Type	Silver

Operating Force (O.F.)	6,67 N [24 oz] max.
Release Force (R.F.)	1,67 N [6.0 oz] min.
Overtravel (O.T.)	10,2 mm [.400 in] min.
Differential Travel (D.T.)	.045 in. approx.
Operating Position (O.P.)	19,6 ± 1,0 mm [0.770 ± 0.040 in]
Free Position (F.P.)	22,4 mm [0.880 ± 0.025 in] max.
Housing Material	Polyester
CE mark	No
UL File #	E12252
CSA File #	LR4442
Agency Approvals and Standards	UL/CSA
Recommended For	Door Status Indication
Availability	Global
Series Name	DM/DP

