

---

Item no.: 2002-3208  
Product description: Triple-deck terminal block 6-conductor through terminal block L without marker carrier gray housing internal commoning conductor entry with violet marking suitable for Ex e II applications

---



Produkt kann von Bild abweichen / product may differ

Packing unit 50 pieces

RoHS compliant

Current intensity EN	28 A
Product group	22 (TOPJOB S RAIL-MOUNTED TERMINAL BLOCKS)
Number of levels	3
Cross section [mm <sup>2</sup> ]	0.25 - 2.5 mm <sup>2</sup>
Cross section [AWG]	22 - 12 AWG
Connection method	CAGE CLAMP®S Connection
Cross section [mm <sup>2</sup> ]	0.25 - 4 mm <sup>2</sup>
Cross section [AWG]	22 - 12 AWG
Wiring method	s + f-st
Connection method	CAGE CLAMP®S Connection
Measured voltage EN	500 V
Measured shock voltage	6 kV
Pollution degree	3
Current intensity EN	24 A
Weight	17.865 g
Color	grey

Wiring type	Front-entry
No. of connection Points	6
No. of potentials	1
Height	69.5 mm
Height	2.736 in
Width	5.2 mm



Width	0.205 in
Depth	93.5 mm
Depth	3.681 in
Strip length from	10 mm
Strip length to	12 mm
Strip length	0.43 in
Customs Tariff No.	85369010
Country of Origin	Deutschland
Mounting	TS 35



Item number	Admission office	Approval no.	Voltage [V]	Current [A]	Cross section [ mm <sup>2</sup> ]
2002-3208	CSA	154112-1536069	600	20	22-12
2002-3208	PTB	IECEXPTB03.0004U	440	19	0,2-4
2002-3208	PTB	PTB03Atex1162U	440	19	0,2-4
2002-3208	RosTest	8189158	440	19	0,2-4
2002-3208	UR	E45172	300	20	22-12

Sorting criteria: admission office - approval number

© WAGO Kontakttechnik GmbH & Co. KG

Specifications are subject to changes and errors may be expected