




2360 LED Flashlight



If you like the convenience of AA alkaline batteries, but need the performance of lithium batteries, the 2360 LED is the light for you. Using 2 standard AA alkaline batteries, the new 2360 LED emits a peak output of 250 lumens. With a run time of up to 2 hours 15 m, the last thing you will need to worry about while on the job, is a dim light or dead batteries. Constructed with the most durable of materials: an aerospace grade aluminum body and an impact resistant LED lamp module, the 2360 LED keeps you on point without equipment failure. High and Low light output is available with a push of the tail button. It features a non-slip textured body for secure handling. The removable two way pocket clip securely attaches the 2360 to your pocket or the brim of your hat.



Materials

Body	Lens	Shroud	Switch Type
Aluminum with Type II Anodized	PC	Aluminum with Type II Anodized	Momentary & On/Off push button w/ three modes - High, Strobe & Low
Clip	Contact, Spring & Retainer	O-Ring	Night Vision Film
High Carbon Steel		EPDM	

Configuration

Cat. #	Description

**2360 LED Flashlight
ANSI FL1 Specifications**

	High	Low
LIGHT SOURCE.	LED	
BATTERIES	2 AA Alkaline (Included)	
CHARGE TIME	N/A	
VOLTAGE	3	
LENGTH	15.7 cm (6.2")	
WEIGHT W/ BATTERIES	0.09 kg (3 oz.)	
WEIGHT W/O BATTERIES	0.1 kg (3.7 oz.)	

LIGHT OUTPUT

RUNTIME (hours/min)

BEAM DISTANCE (meters)

PEAK BEAM INTENSITY (candela)

FL1 STANDARD	High	Low
	2h 15m	
	151m	45 m.
	5692cd	512cd

2360 LED Flashlight Accessories

No accessories are currently available for this product