Datasheet

Stock No: 748-2257

ENGLISH

RS Pro Blue Equipment Wire, 0.75 mm² CSA, 1000 V 18 AWG, 100m

BS 4808

Cable Construction

Conductor	**Tinned Copper**
square(mm2)	0.75
Construction	T0.2±0.008×24
Standard Dia.(mm)	1.13
Insulation	**PVC**
Thickness	0.59
Insulation Dia.(±0.1mm)	2.30 +0.15/-0.1

ENGLISH

Design



Electrical Characteristics

Max.Conductor DC Resistance at 20℃ （Ω/Km）	<25.2
Min.Insulation DC Resistance at 20℃ （MΩ*Km）	200
Rated Temperature(℃)	85
Rated Voltage (V)	1500

Manufactured to BS4800 (Technical Paints British Standards)

Flammability Test: IEC EN60332-1