

Printer - BLUEMARK CLED - 5147999

Please be informed that the data shown in this PDF Document is generated from our Online Catalog. Please find the complete data in the user's documentation. Our General Terms of Use for Downloads are valid (<http://download.phoenixcontact.com>)


Printers with LED-UV technology for printing plastic labels in UniCard format.



Why buy this product

- ✓ Easy and time-saving operation
- ✓ The printer detects the direction of the inserted sheets and automatically rotates printing 180° if required
- ✓ Instant wipe resistance, making the labels ready for immediate use
- ✓ Fast labeling of plastic labels for terminal, conductor, cable, and device marking applications
- ✓ Solvent-free labeling of up to 10,000 markers per hour
- ✓ Environmentally-friendly high-speed printer with modern UV technology
- ✓ Automatic material feed
- ✓ Can be networked via Ethernet

Key commercial data

| | |
|--------------------------------------|---|
| Packing unit | 1 pc |
| GTIN |  4 046356 586177 |
| Weight per Piece (excluding packing) | 16000.0 g |
| Custom tariff number | 84433210 |
| Country of origin | Germany |

Technical data

General

| | |
|-----------|----------------------|
| Interface | 10/100 Mbps Ethernet |
| | USB 2.0 |
| Weight | 16.00 kg |

Dimensions

| | |
|--------|-----------|
| Length | 500.00 mm |
| Height | 330.00 mm |
| Width | 480.00 mm |

Connection data

| | |
|-----------------|----------|
| Minimum voltage | 100 V AC |
|-----------------|----------|

Printer - BLUEMARK CLED - 5147999

Technical data

Connection data

| | |
|-----------------|-----------------|
| Max. voltage | 240 V AC |
| Additional text | 50 Hz ... 60 Hz |

Classifications

eCl@ss

| | |
|------------|----------|
| eCl@ss 4.0 | 24190103 |
| eCl@ss 4.1 | 24190103 |
| eCl@ss 5.0 | 19029102 |
| eCl@ss 5.1 | 19029102 |
| eCl@ss 6.0 | 27141137 |
| eCl@ss 7.0 | 27141137 |
| eCl@ss 8.0 | 27141137 |

ETIM

| | |
|----------|----------|
| ETIM 4.0 | EC001045 |
| ETIM 5.0 | EC001672 |

UNSPSC

| | |
|---------------|----------|
| UNSPSC 6.01 | 43172501 |
| UNSPSC 7.0901 | 43212107 |
| UNSPSC 11 | 43172501 |
| UNSPSC 12.01 | 43212107 |
| UNSPSC 13.2 | 43212107 |

Accessories

Accessories

Magazine

Magazine - BLUEMARK CLED-MAG 20 - 5146655



Magazine for the BLUEMARK CLED printer, for accommodating 20 UC-... or 20 UCT-... sheets

Printer - BLUEMARK CLED - 5147999

Accessories

Magazine - BLUEMARK CLED-MAG 40 - 5146668



Magazine for the BLUEMARK CLED printer, for accommodating 40 UC-... or 40 UCT-... sheets

Magazine - BLUEMARK MAG AI-WM - 5146567



Magazine for BLUEMARK printer, for accommodating 0.5 - 1.5 mm² ferrules with insulating collar that can be labeled

Magazine - BLUEMARK MAG AI-WM 2,5 - 5146640



Magazine for BLUEMARK printer, for accommodating 2.5 mm² ferrules with insulating collar that can be labeled

Planning and marking software

Software - CLIP-PROJECT ADVANCED - 5146040



Multilingual software for easy planning of Phoenix Contact on DIN rails together with the integrated TRABTECH-select software module for planning comprehensive surge protection concepts.

Software - CLIP-PROJECT PROFESSIONAL - 5146053



Multi-lingual software for terminal strip project planning. A marking module allows professional labeling of markers and labels for marking terminal blocks, conductors, cables and devices. The additionally integrated software module TRABTECH-select for planning comprehensive surge protection concepts.

Printing system accessories

Printer - BLUEMARK CLED - 5147999

Accessories

Stackable housing - BLUEMARK CLED-STACKER 20 - 5146656



Stackable housing for the BLUEMARK CLED printer, for accommodating 20 UC-... or 20 UCT-... sheets

Accommodating box for marker sheets - BLUEMARK CLED-BASE - 5146669



Accommodating box, in conjunction with the BLUEMARK CLED-MAG 40, for accommodating 90 UC or UCT sheets

Ink cartridge - BLUEMARK CLED-FLUID-CARTR. - 5146662



Cartridge, for replacement, 20 ml UV color, black, including cleaning cartridge

Case - BLUEMARK CLED CASE - 5146725



Case for the BLUEMARK CLED printer
