

NSYDPLM54T

Glazed door for NSYPLM54T without locking



Main

Range	Thalassa
Accessory / separate part category	Enclosure accessory
Product or component type	Door
Device application	Multi-purpose
For enclosure nominal dimensions	
Mounting location	Front
Range compatibility	Thalassa PLM
Device composition	1 door
Quantity per set	Set of 1

Complementary

Material	Polyester reinforced with fibreglass for door
Colour	Door : grey RAL 7032
Door type	Glazed
Door opening	Left Right 180 °
Maximum load	50 kg/m ²
Height	570 mm
Width	460 mm
Depth	50 mm

Environment

Offer Sustainability

Sustainable offer status	Not Green Premium product
--------------------------	---------------------------

Contractual warranty

Warranty period	18 months
-----------------	-----------

The information provided in this documentation contains general descriptions and/or technical characteristics of the products contained herein. This documentation is not intended as a substitute for and is not to be used for determining suitability or reliability of these products for specific user applications. It is the duty of any such user or integrator to perform the appropriate and complete risk analysis, evaluation and testing of the products with respect to the relevant specific application or use thereof. Neither Schneider Electric Industries SAS nor any of its affiliates or subsidiaries shall be responsible or liable for misuse of the information contained herein.