

CUSTOMER DATA SHEET	Status: Approved
CDS No: 25652, 25654, 25656, 25649, 25650	Date: 21/01/11
Product JACKSON* Safety V20 Purity Eye Protection	Replaces: New

No Photo Available

PRODUCT (All Variants)		
Regulatory Compliance		EN 166:2001
Authorised Body		INSPEC 0194
Optical Class		Class 1 (Continuous Use)
Mechanical Strength		Class F (Low Energy 45m/s)
Extremes of Temperature		T (-5 deg C to + 55 deg C)
Weight		23.0 (g)
Ocular/Lens Type, Scale Filter Numbers (Filter Type)		
Smoke		5-3,1 (Sunglare filter without infra-red specification)
Clear Anti-Fog		2-1.2 (UV Filter colour recognition may be affected)
Indoor/Outdoor		5-1.7 (Sunglare filter without infra-red specification)
Amber		2-1.2 (UV Filter colour recognition may be affected)
Clear		2-1.2 (UV Filter colour recognition may be affected)
Ocular/Lens Markings and Frame Marking		
Lens Variant	Lens	Frame
Smoke (25652)	CE 5-1.1 KC 1 FT	CE KC EN166 FT
Clear Anti-Fog (25654)	CE 2-1.2 KC 1 FT	CE KC EN166 FT
Indoor/Outdoor (25656)	CE 5-1.7 KC 1 FT	CE KC EN166 FT
Amber (25649)	CE 2-1,2 KC 1 FT	CE KC EN166 FT
Clear (25650)	CE 2-1.2 KC 1 FT	CE KC EN166 FT
PACKAGING		
Unit of sale: Corrugated box	1 pair of glasses/poly bag 12 polybags per sales unit and 12 sales units per transit outer (144 pairs of glasses)	
Sales Unit Size 16.5 x 10.6 x 29.8 cm	Net (gross) Weight/Box 0.324 Kg (0.522 Kg)	
ADDITIONAL INFORMATION		
Please refer to the information included in the product insert. Data generated from samples taken to be typical of standard product. The data is given for information only. Additional information can be supplied on request.		
CONFIDENTIALITY STATEMENT		
These specifications and the confidential information contained herein are the property of Kimberly-Clark. Copies of this material are the property of Kimberly-Clark and should be made only if necessary. Copies and original are considered trade secrets.		