

## Cable gland - VC-K-KV-PG16(11,5-15,5) - 1854844

Please be informed that the data shown in this PDF Document is generated from our Online Catalog. Please find the complete data in the user's documentation. Our General Terms of Use for Downloads are valid (<http://download.phoenixcontact.com>)



Half screw connection Pg16, made of plastic, consisting of rubber seal with one hole and one pressure screw, for type 1 housings, cable [mm] 11.5 - 15.5

### Key commercial data

Packing unit	5 pc
Minimum order quantity	5 pc
GTIN	 4 017918 146054
Weight per Piece (excluding packing)	6.1 g
Custom tariff number	39269097
Country of origin	Poland

### Technical data

#### Dimensions

Wrench size, union nut	27 mm
External cable diameter	11.5 mm ... 15.5 mm

#### Ambient conditions

Degree of protection	IP67
Ambient temperature (operation)	-20 °C ... 100 °C

#### General

Note	Adapter screw connections are available on request for large cable dimensions, from Pg16 to Pg21 and from Pg21 to Pg29
Type of the screw connection	Half screw connection
Material, pressure screw	Polyamide
Seal material	TPE
Shielded	No
Thread type on seal side	Pg16
Tightening torque, union nut	5.00 Nm

# Cable gland - VC-K-KV-PG16(11,5-15,5) - 1854844

## Classifications

### eCl@ss

eCl@ss 4.0	27141209
eCl@ss 4.1	27141209
eCl@ss 5.0	27149109
eCl@ss 5.1	27149109
eCl@ss 6.0	27149109
eCl@ss 7.0	27149109
eCl@ss 8.0	27149109

### ETIM

ETIM 2.0	EC000441
ETIM 3.0	EC000441
ETIM 4.0	EC000441
ETIM 5.0	EC000441

### UNSPSC

UNSPSC 6.01	31261502
UNSPSC 7.0901	31261502
UNSPSC 11	31261502
UNSPSC 12.01	31261502
UNSPSC 13.2	31261502

## Approvals

### Approvals

---

Approvals

GOST

---

Ex Approvals

---

Approvals submitted

---

### Approval details

GOST 
--

## Cable gland - VC-K-KV-PG16(11,5-15,5) - 1854844

### Accessories

#### Accessories

Half screw connection

Cable gland - VC-K-KV-PG21-O - 1885363

Half screw connection made of plastic with rubber seal without hole or for individual holes