

LOC	DIST	REVISIONS					
		P	LTR	DESCRIPTION	DATE	DWN	APVD
A1	—		A1	PART NUMBER CHANGED TO TYCO ELECTRONICS	24JAN2001	ACK	GF
			B1	MAT.-COLOUR CHANGE FROM BLUE TO NATURE	30.10.07	M.S	MS
			B2	REVISED PER ECO-10-000445	11JAN09	KK	AEG


CROSS REFERENCE LIST / UEBERSETZUNGSLISTE

TE - PN	OLD PART NUMBER	SEE SHEET		TE - PN	OLD PART NUMBER	SEE SHEET
1 393 546 - 1	C42315-A1347-A101	2		2 1 - 1 393 546 - 1	C42315-A1347-A112	2
1 393 546 - 2	C42315-A1347-A102	2		2 1 - 1 393 546 - 2	C42315-A1347-A116	2
1 393 546 - 3	C42315-A1347-A103	2		1 - 1 393 546 - 3	C42315-A1347-A124	2
1 393 546 - 4	C42315-A1347-A104	2		1 - 1 393 546 - 4	C42315-A1347-A201	3
1 393 546 - 5	C42315-A1347-A105	2		1 - 1 393 546 - 5	C42315-A1347-A202	3
2 1 - 393 546 - 6	C42315-A1347-A106	2		1 - 1 393 546 - 6	C42315-A1347-A203	3
1 393 546 - 7	C42315-A1347-A107	2		1 - 1 393 546 - 7	C42315-A1347-A204	3
1 393 546 - 8	C42315-A1347-A108	2		2 1 - 1 393 546 - 8	C42315-A1347-A205	3
1 393 546 - 9	C42315-A1347-A109	2		1 - 1 393 546 - 9	C42315-A1347-A208	3
1 - 1 393 546 - 0	C42315-A1347-A110	2		2 - 1 393 546 - 0	C42315-A1347-A212	3

ERSETZT EC-ZEICHNUNG C42315-A1347-A1***-27 BL. 1 UND 2
UND C42315-A1347-A2***-27 BL. 1


2

 OBSOLETE PARTS: OBSOLETE CIS STREAMLINING PER D.RENAUD/D.SINISI

THIS DRAWING IS A CONTROLLED DOCUMENT FOR TYCO ELECTRONICS CORPORATION IT IS SUBJECT TO CHANGE AND THE CONTROLLING ENGINEERING ORGANIZATION SHOULD BE CONTACTED FOR THE LATEST REVISION.		DWN G.ACKERMANN	24JAN2001	tyco Electronics		tyco Electronics AMP GmbH D - 67346 Speyer	
DIMENSIONS: mm		CHK M.SCHLEIHAUF	-	NAME DIPFIX - SCHALTER DIPFIX - SWITCH			
		APVD G.FELDMER	-	PRODUCT SPEC			
		APPLICATION SPEC		RESTRICTED TO			
MATERIAL -		WEIGHT -		SIZE A3	CAGE CODE 00779	DRAWING NO C=1393546-1	
FINISH -		CUSTOMER DRAWING		SCALE 1:1	SHEET 1	OF 3	REV B2

LOC	DIST	REVISIONS				
		P	LTR	DESCRIPTION	DATE	DWN APVD
A1	-	-	-	SEE SHEET 1	-	-


View A




1) Beim Kleinmaß 5,08 müssen die
Schalter spiegelbildlich montiert werden
In the case of dim. 5,08 the switches
have to be mounted rear side to rear side

2) ausgeliefert in ausgehaktem Zustand
delivered in unlocked condition


Sollbruchstellen, einzelne
Schalter abtrennbar
Predetermined breaking point,
single switches could be broken off



Rasterlochung und
Packungsdichte Mounting holes and
possible package density



Schaltschema
(Beispiel: 4 Umschalter)



Circuit schematic
(example: 4 changeover switches)



2

TE - PN	OLD PART NUMBER	DIMENSION a	POSITION NUMBER POLZAHL
1 - 1 393 546 - 4	C42315-A1347-A201	5.08	1
1 - 1 393 546 - 5	C42315-A1347-A202	10.16	2
1 - 1 393 546 - 6	C42315-A1347-A203	15.24	3
1 - 1 393 546 - 7	C42315-A1347-A204	20.32	4
1 - 1 393 546 - 8	C42315-A1347-A205	25.4	5
1 - 1 393 546 - 9	C42315-A1347-A208	40.64	8
2 - 1 393 546 - 0	C42315-A1347-A212	60.96	12

ERSETZT EC-ZEICHNUNG C42315-A1347-A2***-27 BL.1

2 OBSOLETE PARTS: OBSOLETE CIS STREAMLINING PER D.RENAUD/D.SINISI

THIS DRAWING IS A CONTROLLED DOCUMENT FOR TYCO ELECTRONICS CORPORATION
IT IS SUBJECT TO CHANGE AND THE CONTROLLING ENGINEERING ORGANIZATION
SHOULD BE CONTACTED FOR THE LATEST REVISION.

DIMENSIONS:	TOLERANCES UNLESS OTHERWISE SPECIFIED:
mm	0 PLC ±
	1 PLC ±
	2 PLC ±
	3 PLC ±
	4 PLC ±
	ANGLES ±°
MATERIAL	FINISH

DWN 24 JAN 2001
G. ACKERMANN
CHK -
M. SCHLEIHAUF
APVD -
G. FELDMEIER
PRODUCT SPEC
APPLICATION SPEC
WEIGHT -

CUSTOMER DRAWING

tyco
Electronics

tyco Electronics AMP GmbH
D - 67346 Speyer

NAME
DIPFIX - SCHALTER
DIPFIX - SWITCH

SIZE	CAGE CODE	DRAWING NO	RESTRICTED TO
A3	00779	C=1393546-1	-

SCALE 5:1, 2:1 SHEET 3 OF 3 REV B2