

4

3


2

1


LOC	DIST	REVISIONS				
P	LTR	DESCRIPTION	DATE	DWN	APVD	
	A	EBD0-0122-04	25FEB04	JMS	FWK	

NOTES


- 1 SINGLE PACK IN ACCORDANCE WITH AMP SPEC 107-3275
- 2 50 TRAY PACK IN ACCORDANCE WITH AMP SPEC 107-3275
- 3 0.08μm Au PLATING OVER 1.27μm Ni PLATING OVER 0.76μm Cu PLATING
- 4 1.27μm Ni PLATING OVER 0.76μm Cu PLATING
- 5 FOR TECHNICAL DATA REFER TO YOUR LOCAL TYCO ELECTRONICS SALES OFFICE
- 6 ALL DIMENSIONS ARE NOMINAL FOR REFERENCE ONLY UNLESS OTHERWISE STATED



RECOMMENDED PCB LAYOUT
WITH MOUNTING POSTS



RECOMMENDED MOUNTING HOL
MAX PANEL THICKNESS: 5.5mm



						1	1	PTFE	INSULATOR	3
						1	1	PHOS BRONZE	CONTACT	2
						1	1	ZINC ALLOY	BODY	1
						5--1	5--0	MATERIAL	DESCRIPTION	ITEM
						2	1			
QUANTITY PER ASSY								PARTS LIST		

THIS DRAWING IS A CONTROLLED DOCUMENT.		DWN J.SANDWELL 25FEB04	tyco Electronics Tyco Electronics Corporation Stanmore, Middlesex, HA7 4RS							
DIMENSIONS: MM		CHK S.PARLOW 25FEB04								
		APVD F.WHEELER-KING 25FEB04	NAME BNC ELBOW BULKHEAD PCB SOCKET LOW PROFILE							
		PRODUCT SPEC 108-3435	50 OHMS DIECAST							
MATERIAL		FINISH	SIZE	CAGE CODE	DRAWING NO	RESTRICTED TO				
-		-	A3	00779	C-1634556	-				
CUSTOMER DRAWING								SCALE NTS	SHEET 1 OF 1	REV A