

Name: **JONO luminaire**
1x35W T5/G5 220-240V 0/50-60Hz, 1500mm
Type: 796-1836



Technical specification

Colour: RAL9010
Material: Base aluminium (RAL9010) / diffuser opal polycarbonate
Electronic control gear: x
Enclosure class: IP44
Length (mm): 1500 mm
Light source: 1xT5 35W/G5
Operating frequency (Hz): 0/50-60 Hz
Rated power (W): 35W
Rated voltage (V): 220-240 V
Weight (kg): 1,850 kg
Dimensions (mm) l x w x h: 1500x55x87 mm

