



Outside dimensions: 330 x 240 x 20 mm (closed)

2300 Service-Set ESD

The green tool folder serves as an electrical dissipative workbench pad of 680 x 680 x 0.35 mm. The surface resistance according to DIN 53482 is approx. 10^8 ohm. The workbench pad has 3 press-stud receptacles for connecting the contact bracelet and the earth wire. With 2 additional press buttons the pad may be closed as tool bag. The 2 patch pockets carry the contact bracelet and the earth wire. Furthermore 16 dissipative tools are placed in pockets, ready to hand. **Weight with tools:** 0.850 kg

No.	Description of individual tools	No.	Description of individual tools
2-166	Glass fibre contact cleaner, with rotary mechanism, plastic casing	5-191	Tweezers made from conductive, black plastic material, reinforced with glass fibre, 120 mm, with rounded tips
2-620	PLCC-extractor	5-194	Tweezers made from conductive, black plastic material, reinforced with glass fibre, 120 mm with bent, pointed tips
3-601-13	Side cutters, 120 mm, semi flush, for soft wire up to 1.5 mm Ø and hard wire up to 0.4 mm Ø, bright steel-polished, box joint, double leaf spring, with dissipative black hand guard	6-616	Socket wrench with dissipative handle, blade made from chrome vanadium, nickel-plated, A/F 3.5 mm
3-633-13	Snipe nose pliers, 120 mm, plain jaws, bright steel-polished, box joint, double leaf spring, with dissipative black hand guard	6-661	TORX screwdriver T 5, with dissipative handle, blade made from chrome vanadium, chrome-plated, with black tip
4-601	Slotted screwdriver with dissipative handle, blade made from chrome vanadium, chrome-plated, with black tip, 50 x 0.8 mm	6-664 L	TORX screwdriver T 8 with bore-hole in the tip, with dissipative handle, blade made from chrome vanadium, chrome-plated, with black tip
4-605	Slotted screwdriver with dissipative handle, blade made from chrome vanadium, chrome-plated, with black tip, 60 x 2.0 mm	6-666 L	TORX screwdriver T10 with bore-hole in the tip, with dissipative handle, blade made from chrome vanadium, chrome-plated, with black tip
4-606	Slotted screwdriver with dissipative handle, blade made from chrome vanadium, chrome-plated, with black tip, 60 x 2.5 mm	9-342	Contact bracelet cloth armband, allergy-free, edges and surface insulating, spiral cord, 1 Mohm safety resistor, combined press-stud and terminal connection, to DIN EN 100 015/1
4-621	Cross-recess screwdriver size 000, with dissipative handle, blade made from chrome vanadium, chrome-plated, with black tip	9-346	Earth wire with 1 Mohm safety resistor, 2500 mm long, with terminal connection resp. press-stud, for connecting workbench pad and floor cover and connection to an earth potential
4-622	Cross-recess screwdriver size 00, with dissipative handle, blade made from chrome vanadium, chrome-plated, with black tip		
4-623	Cross-recess screwdriver size 0, with dissipative handle, blade made from chrome vanadium, chrome-plated, with black tip		