

TECHNICAL SPECIFICATION

Technical Service Department,
JSP Ltd., Worsham Mill, Minster
Lovell, Oxford, OX8 5RX
Tel.: 01993 824000
Fax: 01993 822375

Tradesman 2 A1P2(S)

Product Code:	2144811
New Code:	BKG280005000
Brief Description:	Organic vapour and particulate respirator
Conformity:	Meets the requirements of EN 405.
Performance:	Offers a nominal protection factor (NPF) of 12.5 x Occupational Exposure Standard (OES) for fine toxic dusts, fibres, fumes and aqueous mist also offers protection up to concentrations of 1000 ppm (Parts Per Million) for organic vapours and gases.
Instructions For Use:	Ensure that the mask is fitted properly and in accordance with the instructions supplied. Ensure that the mask chosen is suitable for the intended purpose.
Cleaning Instructions:	Wipe with damp cloth soaked in mild detergent solution, being careful not to get any liquid inside the cartridge. DO NOT USE abrasive substances or solvents.
Maintenance:	Store in an airtight container, away from direct sunlight, chemicals or extremes of temperature. Dispose of unit after 28 days of use.
Limitations of Use:	The mask, when in contact with the skin may cause allergic reactions to susceptible individuals. If this occurs leave the hazard area remove mask and seek medical advice.
Protection mask is not	will only be offered if the mask is fitted correctly. The designed to be worn by people with facial hair.