

ITT 1000 W 235 V-0170 R7S

HALOTHERM | Infrared halogen lamps, quartz clear



Areas of application

- Plastics, paper and printing industries
- Drying paint and varnishes
- Coil coating
- Keeping food warm in restaurants

Product benefits

- Short response time
- High efficiency
- Precise controllability
- Long lamp life



Product datasheet

Technical data


Electrical data

Nominal wattage	1000.00 W
Nominal voltage	235 V
Nominal current	4.3 A
Lamp current	4.30000 A
Construction voltage	235 V

Photometrical data

Color temperature	2350 K
-------------------	--------

Dimensions & weight



Diameter	10.0 mm
Length	327.4 mm
Filament length	270.00 mm

Lifespan

Lifespan	5000 h
----------	--------

Additional product data

Base (standard designation)	R7s
-----------------------------	-----

Capabilities

Burning position	p15
Fuse, quick-acting	6.3 A

Country specific information

Product code	METEL code	SEG-No.	STK number	UK Org
--------------	------------	---------	------------	--------

Product datasheet

4008321203557	OSRHALOTT1000170	-	4739789	-
---------------	------------------	---	---------	---

Product datasheet

Logistical Data

Product code	Product description	Packaging unit (Pieces/Unit)	Dimensions (height x width x length)	Volume	Gross weight
4008321203557	ITT 1000 W 235 V- 0170 R7S	Folding carton box 1	26 mm x 26 mm x 378 mm	0.26 dm ³	48.33 g
4008321203564	ITT 1000 W 235 V- 0170 R7S	Shipping carton box 12	259 mm x 95 mm x 262 mm	6.45 dm ³	687.00 g

The mentioned product code describes the smallest quantity unit which can be ordered. One shipping unit can contain one or more single products. When placing an order, for the quantity please enter single or multiples of a shipping unit.

Disclaimer

Subject to change without notice. Errors and omission excepted. Always make sure to use the most recent release.