

Datasheet

Name: **All-round luminaire**
 2x18W TC-DE/G24q-2 220-240V 0/50-60Hz

Type: 796-1889



Technical specification

Colour:	White
Material:	Polycarbonate
Electronic control gear:	x
Enclosure class:	IP44
Impact resistance (J):	IK06
Light source:	2xTC-DE 18W/G24q-2
Operating frequency (Hz):	0/50-60 Hz
Rated voltage (V):	220-240 V
Weight (kg):	1,150 kg
Dimensions (mm), diameter x height:	320x106 mm
Recessing dimensions:	Ø296x80 mm

