



Product Information

ITP100x40-Ø15 NL40

EAN 4031582324525

Wheel centre made of Aluminium, Tread:
Polyurethane, casted, precision ball bearing

Wheel diameter	100 mm
Width of Tread	40 mm
Axle Hole Ø	15 mm
Hub length	40 mm
Temperature	- 20 / + 60 °C
Standard	EN 12533
Dynamic Load capacity	300 kg
Static Load capacity	600 kg
Hardness of tread	A 92 Shore

