


Stromlaufplan /  
Schematic diagram

|   |                                                                                     |                                                  |                                                                                       |   |
|---|-------------------------------------------------------------------------------------|--------------------------------------------------|---------------------------------------------------------------------------------------|---|
| 1 |    | Litze braun (+) / flexible conductor brown (+)   |    | 1 |
| 2 |    | Litze weiss (Ö) / flexible conductor white (O)   |    | 2 |
| 4 |  | Litze schwarz (S) / flexible conductor black (S) |  | 4 |
| 3 |  | Litze blau (-) / flexible conductor blue (-)     |  | 3 |

Halogen-freie PUR-Leitung 4x0,34mm<sup>2</sup>  
in schwarz mit UL/CSA-Zulassung /  
Halogen-free PUR-conductor 4x0,34mm<sup>2</sup>  
black with approval according to UL/CSA

|                |               |
|----------------|---------------|
| 21 03 415 2401 | 0,3m          |
| 21 03 415 2402 | 0,6m          |
| 21 03 415 2403 | 1,0m          |
| 21 03 415 2404 | 1,5m          |
| 21 03 415 2405 | 2,0m          |
| Artikelnr.     | Nennlänge (L) |



| All Dimensions in mm<br>Original Size DIN A 4 |          |      | Techn. Character.                                   |          |      | Nicht tolerierte Masse / Free size tolerances |                                                                                                   |
|-----------------------------------------------|----------|------|-----------------------------------------------------|----------|------|-----------------------------------------------|---------------------------------------------------------------------------------------------------|
|                                               |          |      |                                                     | Dat.     | Name | 1:1                                           | M12-Rundsteckverbinder<br>Buchse Stift gerade /<br>M12-circular connector<br>female male straight |
|                                               |          |      | Detail.                                             | 22.11.04 | Ho   |                                               |                                                                                                   |
|                                               |          |      | Insp.                                               |          | WELL |                                               |                                                                                                   |
|                                               |          |      | Stand.                                              |          |      |                                               |                                                                                                   |
| 411416                                        | 17.01.05 | Ho   | HARTING Electric GmbH & Co. KG<br>D-32339 Espelkamp |          |      | 1:1                                           | TB 21 03 415 2400                                                                                 |
| 411399                                        | 10.01.05 | Ho   |                                                     |          |      |                                               |                                                                                                   |
| 411338                                        |          |      |                                                     |          |      |                                               |                                                                                                   |
| Mod.                                          | Dat.     | Name |                                                     |          |      | Sub.                                          | Blatt / page                                                                                      |

