



ENGLISH

Datasheet

**RS Pro Aluminium Enclosure, IP66, 125 x 80 x 57mm**

RS Stock No: **760-8963**



## Product Details

RS Pro enclosure measuring 125 x 80 x 57 mm, is IP66 rated and specifically designed for harsh and demanding applications. This watertight series of enclosure is made from die cast aluminium (ALSi12) and it comes with a powder coated grey finish. The enclosure includes a lid and base, captive stainless steel lid screws, a neoprene O-Ring continuous gasket and 4 copper plated earthing screws for grounding. The enclosure meets DIN1725, IEC 60529, NEMA 4X and 6P, UL 508A, UL 50, UL 50E, CE, MIL-STD-810G (Mechanical Vibration and Shock Test), ASTM B117, IEC 62262 and IK 60068-2-75 standards.

## Features and Benefits

- Cover seal temperature stability -40 to +100°C
- DIN rail mounting point
- Wall thickness of 3 mm



**Specifications:**

Body Material	Die Cast Aluminium Alloy
Colour	Natural
External Dimensions	125 x 80 x 57 mm
External Height	57 mm
External Length	125 mm
External Width	80 mm
Flanged	No
Gasket Material	Neoprene
IP Rating	IP66
Lid Colour	Silver Grey
Shielded	No
Finish	Unpainted