

Hospital Grade Tamper- Resistant Duplex GFCI, Red

2095HGTRRED



Hospital Grade Tamper-Resistant GFCI
Receptacle, 10kA SCCR, 20A 125VAC, Red

features & benefits

- Protects children: patented shutter system helps prevent improper insertion of foreign objects.
- Meets 2008 National Electrical Code® Tamper-Resistant requirements.
- SafeLock™ Protection: if critical components are damaged and ground fault protection is lost, power to receptacle is disconnected.
- Prevents line-load reversal miswire: no power to the face or downstream receptacles if wired incorrectly.
- Exceeds UL943 voltage surge requirements; survives 100x the required UL 3kA/6kV voltage surge test cycles.
- FSUL Listed (Federal Specification WC596).
- Trip indicator light (red LED).
- Side or internal screw-pressure-plate back wire with #10 – #14 AWG solid or stranded copper wire.
- Two back wire holes per terminal.
- Ground screw has a back wire clamp for easy installation.
- 1/4" thinner than competitors' GFCIs; leaves more room for wires in the box.
- Mounting screws are shipped captive in the device and wall plate for easier installation.
- High-impact-resistant thermoplastic construction.
- Extra-long strap.
- Button colors match the device face.
- Dual-direction test and reset buttons.
- Class A rated GFCI.
- Supplied with matching TP26 nylon wall plate.
- Tri-drive screws.
- 10kA short circuit rating.
- For covering patents, see www.legrand.us/patents.

specifications

General Info

Color: Red
Available Colors: White, ivory, light almond, red, brown, black, gray
Type: Duplex
Special Features: Tamper Resistant
Style: Decorator

Listing Agencies/Third Party Information

RoH S: No
CSA Standard: C22.2 No. 42, 144
CUL Listing No: E42190
cULus: Yes
cUL Standard: Yes
Federal Spec: Yes
Fed Spec Number: WC596
UL Listing No: UL498
UL Listed: Yes
UL Standard: Yes
UN SPS C: 39121614

Dimensions

Depth U S: 1.13"
Height U S: 4.2"
Length U S: 4.20"
Width U S: 1.72"

Technical Information

Amps: 20A
NEMA Configuration Number: 5-20R
NEMA Rating: WD-1, WD-6
Volts: 125V
Volts A C: 125
Grade Type: Hospital

Buy American Act Compliance

Country of Origin: CHINA
Buy American Act Status: No