



ENGLISH

Datasheet

IP66 Wall Box with Plain Door, 304 Stainless Steel, Unpainted, 500 x 600 x 200mm

RS Stock number 758-6980



IP66 Wall Boxes

These wall boxes are constructed from 1.2mm AISI 304 natural finish stainless steel and have an IP66 rating. The door of the enclosure has a pull out hinge which allows it to be removed for easy access. The stainless steel door lock and bezel prevent contaminant build-up on the enclosure.

Pull out hinge pins allow door to be completely removed for access

Stainless steel door lock and bezel prevent contaminant build-up

Double lip edge to ensure higher strength and ease of installation for the panel builder

Earth Studs provided on body, door and chassis plate

Hinges are located on the side corresponding to the "Height" dimension

Material 304 / 1.4301 stainless steel

IP66 protection

Note

Each wall box is supplied with either 1, 2 or 3 locks dependant on size of door.

Body Material	304 Stainless Steel
Chassis Plate	Yes
Colour	Unpainted
Door Lock Type	Quick Release Lock
Door Type	Plain
External Depth	200mm
External Dimensions	500 x 600 x 200mm
External Height	500 mm
External Width	600 mm
Fixing Kit	No
Gland Plate	No
IP Rating	IP66