



New generation slide & neg scanner with 2.4" LCD screen and Lith-ion battery

Format	35mm & 110mm slide and negative (3x trays included)
Compatibility	No PC needed. Can work as stand-alone capture device stored on SD card
Scanning Speed	Simple one touch instant preview. 0.5 second scan speed. 2 sec in AP enhance mode.
Image Sensor	5 Mega Pixel CMOS Lens - 3600DPI interpolated
Interface	High Speed USB 2 Connection (Not USB 1.1)
Lens	High Quality 4 Glass Element
Focus Range	Auto Focus with Backlight Exposure
Colour Balance	Auto Balance using Colourbright™ Technology
Tray System	Multi Directional Tray Insert for Increased Convenience
Light Source	Back Light
Power	Powered from USB 2 Socket or use built in Lith-ion battery
Screen	2.4 " Full Colour preview screen. Tidy away flap design
Dimensions	Small Ultra Compact Footprint. (L x W x H) 100mm x 100mm x 150mm
Operating system	Compatible With Windows 2000, XP, Vista and Mac O/S
Other	1 Year limited veho warranty. CE & ROHS compliant

