

## Data sheet

Commercial Art.No.: 92.030.5353.0

Distributor GST18i3V 5P1 F V WS

Distribution block GST18i3, 3 pole, 1 input, 5 outputs, with mounting option, 250 V, 20 A, colour of coding: white



Commercial Art.No.	92.030.5353.0
EAN	4015573437265
Order Unit	1

Certificates / Approvals



## Technical data

### General

Rated current	20 A
Rated voltage	250 V
Rated impulse voltage	4 kV
Pollution degree	2
Mechanical coding	Code 1
Lockable	Yes
Color of coding/ contact carrier	White
Marking of poles	L, N, PE

### Model

Number of inputs	1
Number of outputs	5
Type of fastening	Yes
Degree of protection (IP)	IP20
Type of distributor	HH-Distributor

### Material

Housing material	Polyamide
Halogen free	Yes
Contact material	CuZn
Fire load	0.223 kWh
Insulation components continuous temperature	100 °C
Surface finish	Silver-plated

### Classification

ECLASS 8.1	27440603
ETIM 7.0	EC002567
ETIM 6.0	EC002567

ETIM 5.0	EC002567
ETIM 4.0	EC002567

**Dimensions**

Length	44 mm
Width	52 mm
Height	52.5 mm

**Accessories**

Commercial Art.No.:	Article-type description:	Description:
---------------------	---------------------------	--------------

**Fits with**

Commercial Art.No.:	Article-type description:	Description:
---------------------	---------------------------	--------------