

Shafts

The type and ordering numbers are for one piece

Shaft length [mm]	H [mm]	Suitable for switches	Type	Order number	Delivery batch [pcs]	Weight/unit [kg]
For selector type handles. Shaft diameter 6 mm.						
85	See dimension drawings	OT16...125F	OXS6X85	1SCA101647R1001	10	0.02
105		OT16...125F	OXS6X105	1SCA108043R1001	10	0.02
120		OT16...125F	OXS6X120	1SCA101654R1001	10	0.03
130		OT16...125F	OXS6X130	1SCA101655R1001	10	0.03
160		OT16...125F	OXS6X160	1SCA101656R1001	10	0.04
180		OT16...125F	OXS6X180	1SCA101659R1001	10	0.04
250		OT16...125F	OXS6X250	1SCA101660R1001	10	0.05
330		OT16...125F	OXS6X330	1SCA101661R1001	10	0.05
For round padlockable type handles. Shaft diameter 6 mm.						
60	See dimension drawings	OT16...125F	OX6X60	1SCA111459R1001	10	0.02
85		OT16...125F	OX6X85	1SCA111274R1001	10	0.02
105		OT16...125F	OX6X105	1SCA111930R1001	10	0.02
115		OT16...125F	OX6X115	1SCA111931R1001	10	0.03
130		OT16...125F	OX6X130	1SCA111460R1001	10	0.03
155		OT16...125F	OX6X155	1SCA111275R1001	10	0.04
200		OT16...125F	OX6X200	1SCA111932R1001	10	0.04
300		OT16...125F	OX6X300	1SCA111933R1001	10	0.05
For pistol type handles. Shaft diameter 6 mm.						
150	See dimension drawings	OT16...125F	OX6X150	1SCA022295R5600	10	0.05
170		OT16...125F	OX6X170	1SCA108224R1001	10	0.05
265		OT16...125F	OX6X265	1SCA108225R1001	10	0.08
400		OT16...125F	OX6X400	1SCA108226R1001	10	0.12
Shaft diameter 6 mm ¹⁾						
130	105 ... 135	OT160	OX6X130	1SCA022057R0570	10	0.04
150	125 ... 155	OT160	OX6X150	1SCA022295R5600	10	0.05
210	185 ... 215	OT160	OX6X210	1SCA022295R6080	10	0.06
130	109...174	OT200...250	OX6X130	1SCA022057R0570	10	0.04
150	129...194	OT200...250	OX6X150	1SCA022295R5600	10	0.05
161	140...205	OT200...250	OX6X161	1SCA022067R1760	10	0.05
210	189...254	OT200...250	OX6X210	1SCA022295R6080	10	0.06
290	269...334	OT200...250	OX6X290	1SCA022042R6370	10	0.08
Shaft diameter 12 mm						
166	146...226	OT315...400	OX12X166	1SCA022325R7100	1	0.20
185	165...245	OT315...400	OX12X185	1SCA022325R6710	1	0.20
250	230...310	OT315...400	OX12X250	1SCA022325R6980	1	0.28
280	260...340	OT315...400	OX12X280	1SCA022137R5140	1	0.30
325	305...385	OT315...400	OX12X325	1SCA022042R5810	1	0.36
395	445...525	OT315...400	OX12X395	1SCA022042R5990	1	0.43
465	439...519	OT315...400	OX12X465	1SCA022042R6020	1	0.51
535	515...595	OT315...400	OX12X535	1SCA022042R6110	1	0.59
250	230...345	OT630...800	OX12X250	1SCA022325R6980	1	0.28
280	260...375	OT630...800	OX12X280	1SCA022137R5140	1	0.30
325	305...420	OT630...800	OX12X325	1SCA022042R5810	1	0.36
395	375...490	OT630...800	OX12X395	1SCA022042R5990	1	0.43
465	445...560	OT630...800	OX12X465	1SCA022042R6020	1	0.51
535	515...630	OT630...800	OX12X535	1SCA022042R6110	1	0.59
250	226...355	OT1000...2500	OX12X250	1SCA022325R6980	1	0.28
280	256...385	OT1000...2500 ²⁾	OX12X280	1SCA022137R5140	1	0.30
325	301...430	OT1000...2500 ²⁾	OX12X325	1SCA022042R5810	1	0.36
395	371...500	OT1000...2500 ²⁾	OX12X395	1SCA022042R5990	1	0.43
465	441...570	OT1000...2500 ²⁾	OX12X465	1SCA022042R6020	1	0.51
535	511...640	OT1000...2500 ²⁾	OX12X535	1SCA022042R6110	1	0.59
325	340...535	OETL3150	OX12X325	1SCA022042R5810	1	0.36
395	410...605	OETL3150	OX12X395	1SCA022042R5990	1	0.43
465	480...675	OETL3150	OX12X465	1SCA022042R6020	1	0.51
535	550...745	OETL3150	OX12X535	1SCA022042R6110	1	0.59

¹⁾ Longer shafts on request

²⁾ Wide versions OT1000-1600W
- with shafts over 280 mm, shaft tube OXT20x210X must be used, see page 31