



ENGLISH

Datasheet

**RS Pro Green Nylon Sheet, 500mm x 500mm x 20mm**

RS Stock No: **771-235**



## Product Details

RS Pro nylon sheet in green colour measures, 500 x 500 x 20 mm and has excellent hardness, durability and creep resistance qualities. It is perfect for bush, bearing, roller and wheel applications.

## Features and Benefits

- Typical frictional coefficient half that of other lubricated nylons
- High resistance to water absorption
- Excellent hardness, durability and creep resistance qualities
- Free cutting properties enable tight machining tolerances
- Comes in green colour

**Specifications:**

Colour	Green
Flammability Rating	UL 94 HB
Material	Nylon
Density	1.15 g/cm <sup>3</sup>
Elongation	40%
Length	500 mm
Maximum Operating Temperature	+180°C
Thickness	20 mm
Water Absorption	6%
Width	500 mm
Tensile Strength	70 MPa