

### General Information

Extended Product Type:	PS3-2-1
Product ID:	1SAM101937R0022
EAN:	4013614313868
Catalog Description:	PS3-2-1 3-Phase Busbar
Long Description:	PS3-2-1 Busbar for 2 devices+aux.cont.

### Categories

Products » Low Voltage Products and Systems » Control Products » Manual Motor Starters » Manual Motor Starters Accessories

### Ordering

EAN:	4013614313868
Minimum Order Quantity:	1 piece
Customs Tariff Number:	85369085

### Container Information

Package Level 1 Width:	46 mm
Package Level 1 Length:	120 mm
Package Level 1 Height:	80 mm
Package Level 1 Gross Weight:	0.43 kg
Package Level 1 EAN:	4013614487965
Package Level 1 Units:	10 piece

### Dimensions

Product Net Width:	107.5 mm
Product Net Height:	31.5 mm
Product Net Depth:	13 mm
Product Net Weight:	0.04 kg

### Technical

Rated Operational Voltage:	690 V
Rated Operational Current (I <sub>e</sub> ):	63 A
Standards:	IEC/EN 60947-1 IEC/EN 60947-4-1 UL 60947-1 UL 60947-4-1
Product Name:	3-Phase Busbar
Suitable For:	MS325 MO325
Suitable for Product Class:	Manual Motor Starters

### Environmental

Ambient Air Temperature:	Operation -20 ... +50 °C Storage -20 ... +70 °C
RoHS Status:	Following EU Directive 2002/95/EC August 18, 2005 and amendment

### Technical UL/CSA

Maximum Operating Voltage UL/CSA:	Main Circuit 600 V
Ampere Rating UL/CSA:	63 A

### Certificates and Declarations (Document Number)

cUL Certificate:	1SAA963001-1701
Declaration of Conformity - CE:	1SAD938509-0056
GOST Certificate:	1SAA918000-2703
RoHS Information:	1SAA918001-4402
UL Certificate:	1SAA963001-1602

### Classifications

eClass:	7.0 27379201
E-nummer:	3111432
Object Classification Code:	W
UNSPSC:	39121100

