


**Ordering number C11793\_ANNA-40-4-S**

Family	Anna-40-4	FWHM	12 degrees
Type	Lens array	Efficiency	90 %
LED	Oslon SSL 150	cd/lm	13.700
Color	Clear	Gerber File	Available
Diameter	40 mm		
Height	10.7 mm		
Style	Round		
Optic Material	PMMA		
Holder Material	-		
Fastening	Pin, glue		
Status	Ready		

**Ordering number C11794\_ANNA-40-4-M**

Family	Anna-40-4	FWHM	22 degrees
Type	Lens array	Efficiency	89 %
LED	Oslon SSL 150	cd/lm	4.000
Color	Clear	Gerber File	Available
Diameter	40 mm		
Height	10.7 mm		
Style	Round		
Optic Material	PMMA		
Holder Material	-		
Fastening	Pin, glue		
Status	Ready		

**Ordering number C11795\_ANNA-40-4-W**

Family	Anna-40-4	FWHM	34 degrees
Type	Lens array	Efficiency	89 %
LED	Oslon SSL 150	cd/lm	2.000
Color	Clear	Gerber File	Available
Diameter	40 mm		
Height	10.7 mm		
Style	Round		
Optic Material	PMMA		
Holder Material	-		
Fastening	Pin, glue		
Status	Ready		

**NOTE: The typical divergence will be changed by different color, chip size and chip position tolerance. The typical total divergence is the full angle measured where the luminous intensity is half of the peak value.**



**PRODUCT DATASHEET**  
**Anna-40-4 series**  
last update 27/3/2012



**GENERAL INFORMATION**

- Product series especially designed & optimized for Oslon SSL 150 series of LEDs.
- Special care taken to make light distribution as uniform as possible.
- Lens material optical grade PMMA with high UV and temperature resistance. Allows use of high current and temperature conditions.

Please find more information about used material from below:

[http://ledil.fi/sites/default/files/Documents/Technical/Material/PMMA%20N%20UL94\\_Yellow%20Card.pdf](http://ledil.fi/sites/default/files/Documents/Technical/Material/PMMA%20N%20UL94_Yellow%20Card.pdf)

<http://ledil.fi/sites/default/files/Documents/Technical/Material/PMMA%20N%20PLEXIGLAS-Datasheet.pdf>

D


C

B


A

4


4




Anna-3




Anna-4




Anna-5




Anna-6



Anna-7



Same top side in all versions




3

3

Material: PMMA

- Versions:
- Anna-3-S
  - Anna-3-M
  - Anna-3-W
  - Anna-4-S
  - Anna-4-M
  - Anna-4-W
  - Anna-5-S
  - Anna-5-M
  - Anna-5-W
  - Anna-6-S
  - Anna-6-M
  - Anna-6-W
  - Anna-7-S
  - Anna-7-M
  - Anna-7-W



Number of cones varies; 3, 4, 5, 6 and 7pcs on bottom side depending the version.

Same led-circle in all versions

2

2

This drawing is our property. It can't be reproduced or communicated without our written agreement.



L T F F e i n e i n

DRAWING TITLE

Datasheet Anna40-series Lens

1

1

DRAWN BY p	DATE 12.10.2010
CHECKED BY s n	DATE 12.10.2010
DESIGNED BY hh	DATE 30.07.2010

SIZE A4	DRAWING NUMBER -	REV 1
SCALE 1:1	WEIGHT (g)	SHEET 1/1

D

A