

CRINT interface relay sockets

P/N: 2824489, 2824490, 2824491, 2824492, 2824493, 2824494, 2824495, 2824496, 2824497, 2824499

Features

- Push-in and Screw terminal versions
- Various combinations available
- LED status indicator
- Works with AC or DC



RS Professionally Approved Products bring to you professional quality parts across all product categories. Our product range has been tested by engineers and provides a comparable quality to the leading brands without paying a premium price.

Product Description

Sockets for use with 1 pole PCB mounted relays

General Specifications

Terminals	Push-in/ Screw
LED	Yes
length	89 (push-in) 97.5 (screw)
width	6.2
Height	73 (push-in) 76.9 (screw)
Weight	25g
Ambient temperature storage	-40 ... 85 °C
Ambient temperature operation	-40 ... 70 °C

Electrical Specifications

Rated control voltage	24VAC/DC - 240VAC/DC
------------------------------	----------------------

Protection Category

--	--

Classification

eCl@ss (Version)	
UNSPSC (Version)	

Approvals

Declarations	cURus
Standards Met	VDE

Similar Products

Stock No.	Brand	Product Name	Attribute 1	Attribute 2	Attribute 3
XXX-XXXX	RS PRO				
XXX-XXXX	RS PRO				