





THIS DRAWING IS UNPUBLISHED.

RELEASED FOR PUBLICATION

© COPYRIGHT BY TYCO ELECTRONICS CORPORATION. ALL RIGHTS RESERVED.

LOC	DIST	REVISIONS			
		P	LTR	DESCRIPTION	DATE
J	—		E2	REVISED	11JAN06
				ECR-06-000562	TS
					KB



NOTES;

- 1 MUST BE KEPT BETWEEN $\triangle$ AND 2mm
- 2 THE MATING CAP HSG. PART NUMBER; 175444, 175448
- 3 APPLIED CONTACT P/N 173630, 173631
- 4 APPLICABLE PRODUCT SPEC NO. 108-5280

注:

- 1 $\triangle$ $\triangle$ 面より2mmの範囲で測定
2. 嵌合相手ハウジング型番: 175444, 175448
3. 内装するリセプタクルコンタクト型番は173630, 173631
4. 適用製品規格番号 108-5280

OBSOLETE	淡灰 (LIGHT GRAY)	6-175442-6
	灰色 (GRAY)	175442-6
OBSOLETE	青 (BLUE)	175442-5
	白 (WHITE)	175442-1
	色 (COLOR)	P/N

THIS DRAWING IS A CONTROLLED DOCUMENT.		DWN M.KADOSAKI 16JUN2005	tyco Electronics Tyco Electronics AMP K.K. Kawasaki, Japan	
DIMENSIONS: 単位: 概 mm		CHK T.SHINOHARA 16JUN05		
TOLERANCES UNLESS OTHERWISE SPECIFIED: 一般公差		APVD K.BETSUI 16JUN05	NAME 名称 12Pos. PLUG HOUSING	
0 PLC ± - 1 PLC ± - 2 PLC ± - 3 PLC ± - 4 PLC ± - ANGLES ± -		PRODUCT SPEC 製品規格	.040/.070 HYBRID I/O CONN. (POWER)	
MATERIAL 材料 PBT		APPLICATION SPEC 取付適用規格	12極 プラグハウジング .040/.070 ハイブリッド I/O コネクタ (パワー用)	
		WEIGHT	SIZE A3	CAGE CODE 00779
		CUSTOMER DRAWING	DRAWING NO C-175442	RESTRICTED TO —
			SCALE 尺度 2:1	SHEET 1 OF 1
				REV E2

一般公差 (GENERAL TOLERANCE)
0<≦ 10 : ±0.2
10<≦ 30 : ±0.25
30<≦ 100 : ±0.3
ANGLES : ±3°