



ENGLISH

RS Pro PVC 10m Long Green Flexible Ducting Reinforced, 150mm Bend Radius , Applications Various

RS Stock No. 327-8240

Brand RS Pro



Image representative of range

Product Details

Medium Duty PVC Suction and Delivery Hose

An RS brand of PVC hosing designed with a rigid PVC spiral. Flexible and easy to handle, this hosing has excellent crush resistance and is suitable for use in all weathers. It is ideally used within the agricultural industry as tanker slurry hose, injector hose, irrigator and grain animal feed.

White spiral helix in an opaque green PVC

Multi-purpose for medium duty suction and discharge

Excellent weathering and good crush resistance

Suitable for many liquids, slurries, light solids and dilute chemicals

Temperature range -25°C to +55°C

Note

All data refers to performance at 18°C. Any changes in temperature will affect the performance data.



Suction & Delivery Hose

Specifications

Not what you're looking for? Select the attributes you require, then click the button below

<input type="checkbox"/>	Inner Diameter	38mm
<input type="checkbox"/>	Material	PVC
<input type="checkbox"/>	Length	10m
<input type="checkbox"/>	Suitable Applications	Agriculture, Chemical, Grain, Irrigator, Waste Water Hose
<input type="checkbox"/>	Colour	Green
<input type="checkbox"/>	Bend Radius	150mm
<input type="checkbox"/>	Reinforced	Yes