

Datasheet

RS Pro NCC Series Shielded SMD Common Mode Choke with a Ferrite Core, $\pm 25\%$ Wire-Wound 400mA Idc

RS Stock No: 742-3479



Product Details

RS Pro SMD common mode choke withstands DC current up to 400 mA. This wire-wound choke includes a ferrite core. It is suitable for both flow and reflow soldering.

Features and Benefits

- Low profile
- Surface mountable construction
- Lead free

Specifications:

Core Material	Ferrite
Inductor Construction	Wire Wound
Moulded	Yes
Shielded	Yes
Depth	1.6 mm
Dimensions	3.2 x 1.6 x 2 mm
Height	2 mm
Length	3.2 mm
Maximum DC Current	400 mA
Maximum DC Resistance	300 mΩ
Maximum Operating Temperature	+125°C
Minimum Operating Temperature	-40°C
Tolerance	±25%
Package/Case	1206
Package Type	Tape & Reel