

Audio Connector, Plug, Inline Socket, 3.5 mm, 3-pole, solder terminal, insulated



Description

- Solder terminal: for cable mounting
- Audio entrances and exits
- Data and Signal transfer
- Audio Plug: 3-pole, insulated, straight

Weblinks


[pdf-datasheet](#), [html-datasheet](#), [General Product Information](#), [RoHS](#), [CHINA-RoHS](#), [REACH](#), [Mating Connectors](#), [e-Shop](#), [SCHURTER-Stock-Check](#), [Distributor-Stock-Check](#)

Technical Data


Diameter	3.5 mm
Number of Poles	3-pole
Ratings DC	0.5 A / 30VDC
Ratings AC	0.5 A / 30VAC
Dielectric Strength	500VDC
Insulation Resistance	> 100 MΩ @ 500VDC

Allowable Operation Temp.	-20 °C to 70 °C
Terminal	solder terminal nickel-plated
Housing	insulated
Style	straight
Lifetime	5000 Insertions


Dimensions



Cable diameter max. 4.0 mm



Diagrams



All Variants

Product group	Diameter [mm]	Number of Poles	Terminal	Order Number
Audio Plug/Sockets	3.5	3-pole	solder terminal	4832.3300

Most Popular.

Availability for all products can be searched real-time: <http://www.schurter.com/en/Stock-Check/Stock-Check-SCHURTER>

Packaging unit 100 Pcs

Mating Inlets/Plugs

Category / Description

[Audio Plug/Sockets Overview complete](#)



Audio Connector, Plug, 3.5 mm, 3-pole, solder terminal, shielded	4832.1300
Audio Connector, Plug, 3.5 mm, 3-pole, solder terminal, insulated	4832.1310
Audio Connector, Plug, 3.5 mm, 3-pole, solder terminal, insulated, angled	4832.1320
Audio Plug/Sockets further types to 4832 Audio-Stecker, D=3,5mm	