



10857 - OT*Q35MR16 240V GU10 FL GEST BX1/10 MIC

• Specifications

General characteristics:

Wattage [W]	35
Voltage [V]	240
Cap/Base	GU10
Bulb Shape	MR
Bulb Diameter [mm]	50
Colour temperature [K]	2700
Colour Rendering Index (CRI) [Ra]	100
Rated Life [h]	2000
Dimming Capability	Yes
Coil type	CC-2V
Beam Angle [°]	36
Center Beam Candlepower [cd]	400
Maximum Overall Length [mm]	55
DUN Code	20043168108571
EAN Code	0043168108577
Net weight per piece [g]	44
Gross weight per piece [g]	58
Pack Quantity	10
Inner pack type	BOX
Layer quantity EUR (PC)	800
Layer quantity UK (PC)	1200
Pallet quantity EUR (PC)	2400
Pallet quantity UK (PC)	3600
Outer case size	270 x 110 x 66 (mm)
Brand	General Electric (GE)
Product status	Available