

Model : LT-26HLF

Item	Specification		Item	Specification		
Size	Visible Diagonal	26 Inch	Aspect Ratio	16:9	O	
System	PAL/SECAM I, B/G, D/K	O	OSD	Halftone		
	SECAM L/L'	O		Enhanced(icon type)	O	
	NTSC 4.43(AV)	O		Menu	O	
Power	AC/DC Adapter	110/220V		Multi Language	O	
		AC 50/60Hz		Program List/Edit	O	
	Power Consumption	130W	AV*in	O		
Tuning	ST*BY Power Consumption	Below 3W	AV*out	O		
	FS181 Program		S*Video in	O		
	FVS 100 Program	O	SCART(Full/Half)	2(Full/Half)		
Video	Auto/Manual Programming	O	External Connection	Headphone*out	O	
	Progressive Scan	O		Woofers*out	O	
	PSM (Dynamic,Standard,Mild,Game,User)	O		DVI*in(D1)	O	
	Digital Comb Filter	4H		PC*in(D*sub)	O	
	Engine			PC Audio*in	O	
Sound	DCTI/DLTI	O		User Convenient	Teletext(TOP/FLOF)	/O
	Stereo(A2,NICAM)	O			Teletext Page(Optional)	256
	Equalizer	O			Caption(English)/V*Chip	
	AVL(Auto Volume Leveller)	O			On/Off time	
	Sound Output(RMS)	10W x 2			PIP/DW/Scan	O
Resolution	WXGA	1280 x 768	Optical		Q.View	O
					SSM (Flat,Music,Movie,Speech,User)	5MODE
					ARC(Aspect Ratio Control)	O
			Auto AV		O	
			DTV Built*in(Optional)			
			Viewing Angle	H:170 / V : 170		
			Luminance	500 cd/m ² (Typ.)		
			CR(Contrast ratio)	450:1		

Dimensions(mm)			Weight(kg)	
SET SIZE (W*D*H)	SET SIZE with STAND (W*D*H)	BOX SIZE (W*D*H)	SET+STAND	Packing
768*102*442	768*215*499	870*320*600	11.2	16

Response time : 15ms