

Professionally approved products.

Datasheet

VGA Splitter (4 Port)

RS Stock number 783-9861



Short Description	4 Port VGA Splitter, 450Mhz, up to 65Mtr
Full Description	<p>The NLKVS-range of Video Splitters are designed for desktop use, supplied in a durable, compact metal housing. The splitters duplicate and boost the input signal to 2, 4 or 8 VGA, SVGA or Multi-sync Monitors, with a signal rate of 450 Mhz. Video Splitters are ideal for applications such as tradeshows, business meetings and demonstrations.</p> <p>These products are independent of software and other than cables and Monitors, no additional hardware is required.</p>
Extra Information	<p>Specification 250 - 450Mhz Video Bandwidth 4 Port Supports up to 2048 x 1536 Resolution Supports DDC, DDC2 & DDC2B(Port 1 only) Duplicate one signal input to multiple outputs Ability to be cascaded Effective transmission distance: 65 Mtrs Power saving mode Metal Case</p> <p>Contents 1 x Video Splitter 1 x Power Supply 1 x User Manual</p>