

151-00174



Article Number: 151-00174

Edge Clip Cable Clamp, Panel Thickness .04" -.012 " PA66HIR Black 250/pk



Base Data

Local Order Number 151-00174

Type EC39

Color Black (BK)

Features and Benefits HellermannTyton's edge clips are designed specifically to route bundles by securing them to the edge of a plastic or metal sheet without the need for a mounting hole. The clip is easy to secure and the extraction force is high due to the integrated metal clamp that holds the edge clip in place.

Fixation Method (FF) Edge Clips

Short Description Edge Clip Cable Clamp, Panel Thickness .04" -.012 " PA66HIR Black 250/pk

Product Dimensions

Attaches to Diameter (imperial) 0.6 " - 0.63 "

Bundle Diameter min (imperial) 0.614 "

Bundle Diameter min (metric) 15.3 mm

Bundle Diameter max (imperial) 0.63 "

Bundle Diameter max (metric) 15.9 mm

Panel Thickness max. (imperial) 0.12 "

Panel Thickness max. (metric) 3.0 mm

Panel Thickness min. (imperial) 0.04 "

Panel Thickness min. (metric) 1.0 mm

Nominal Diameter (imperial) 0.62 "

Nominal Diameter (metric) 15.6 mm

Attaches to Diameter (metric) 15.3 - 15.9 mm

Logistics and Packaging

Quantity per bag

Package Quantity 250

Carton Quantity 2500

Material and Specifications

Material Polyamide 6.6 high impact modified (PA66HIR)

Material Shortcut PA6HIR

Flammability UL94 HB

Operating Temperature -40 °F to +176 °F (-40 °C to +80 °C)

ROHS Conformity Yes

