

Product Information



5925UAI075L51-10 DM22 RL9006

EAN 4031582311174

Swivel castor with wheel brake, housing made of Polyamide, with blind hole for furniture fittings.

Wheel centre made of Polyamide, Tread: Polyurethane, plain bearing

Technical Data	
Wheel diameter	75 mm
Width of Tread	10 mm
Castor width	64 mm
Centre hole	10 mm
Dome-Ø	22 mm
Swivel Interference	160 mm
Overall height	76 mm
Temperature	- 10 / + 40 °C
Standard	EN 12528
Weight	0.202 kg
Swivel Radius	80 mm
Hardness of tread	A 87 Shore
Load capacity	80 kg
Load capacity (static)	160 kg



Roll performance	+	+	+	+	+
Movement noise	+	+	+	+	+
Attrition	+	+	+	+	+
Corrosion resistance	+	+	+	+	+

Product Information



5925UAI075L51-10 DM22 RL9006

EAN 4031582311174

