

4

3

2

1

THIS DRAWING IS UNPUBLISHED.

RELEASED FOR PUBLICATION

,19 .

© COPYRIGHT 19

BY AMP INCORPORATED. ALL RIGHTS RESERVED.

LOC

DIST

REVISIONS

G

14

P

LTR

DESCRIPTION

DATE

DWN

APVD


N

REV / REDRAWN / 0720-0482-95 & 0720-0002-95

14FEB95

LO

ME



1. USE FOR AN UNSTRIPPED (SINGLE)
WIRE END ONLY

2. WIRE INSUL DIA, 1.22-1.91 [.048-.075]

-	-	-
100	LOOSE PIECE, BOX	8-324484-1
1000	LOOSE PIECE	324484
QTY	PACKAGE TYPE	PART NO

AMP INCORPORATED
CUSTOMER SERVICE SYSTEM

FOR ADDITIONAL
PRODUCT INFORMATION OR
COPIES OF DRAWINGS
AND TECHNICAL DOCUMENTS

PRODUCT INFORMATION CENTER
1-800-522-6752

FOR APPLICATION
TOOLING INFORMATION

TOOLING ASSISTANCE CENTER
1-800-722-1111

FOR ORDER ENTRY

1-800-526-5142


MAX RECOMMENDED OPERATING
TEMPERATURE:
105°C [221°F]

VOLTAGE RATING:
-

CIRCULAR MIL AREA:
-

THIS DRAWING IS A CONTROLLED DOCUMENT FOR AMP INCORPORATED.
IT IS SUBJECT TO CHANGE AND THE CONTROLLING ENGINEERING
ORGANIZATION SHOULD BE CONTACTED FOR THE LATEST REVISION.

DIMENSIONS:
mm [in]



MATERIAL
BODY, CU PER ASTM B152
INSUL, NYLON, COLOR,
TRANSPARENT

TOLERANCES UNLESS
OTHERWISE SPECIFIED:

0 PLC ±-
1 PLC ±-
2 PLC ±0.20 [.008]
3 PLC ±-
4 PLC ±-
ANGLES ±-

FINISH
BODY, TIN PLATE
PER MIL-T-10727

DWN
L OLMEDA

14FEB95

CHK

M ELLIS

14FEB95

APVD

T MICHIELUTTI

PRODUCT SPEC

APPLICATION SPEC

WEIGHT

-

CUSTOMER DRAWING

AMP

AMP Incorporated
Harrisburg, PA 17105-3608

NAME

SPARE WIRE CAP, TRANSPARENT

SIZE

CAGE CODE

DRAWING NO

A3

00779

C-324484

SCALE 8:1

SHEET 1 OF 1

REV N