
Item no.: 224-114
Product description: 2-CONDUCTOR LIGHTING CONNECTOR; VERSION FOR
INCREASED CONTINUOUS SERVICE TEMPERATURE OF
120°C; CAGE CLAMP®CONNECTION



Packing unit 100 pieces

Product group	7 (Push Wire Conn.)
Cross section from [mm²]	1 mm²
Cross section to [mm²]	2,5 mm²
Cross section from [AWG]	14 AWG
Cross section to [AWG]	12 AWG
Wiring method	e
Connection method	CAGE CLAMP®CONNECTION
Number of strands	2
Cross section from [mm²]	0,5 mm²
Cross section to [mm²]	2,5 mm²
Cross section from [AWG]	20 AWG
Cross section to [AWG]	16 AWG
Wiring method	e+f
Measured voltage EN	400 V
Measured shock voltage	4 kV
Pollution degree	2
Current intensity EN	24 A
Weight	2,74 g
Color	black
Wiring type	Side-entry
No. of connection Points	3
No. of potentials	1



Height	0,61 in
Width	9,5 mm
Width	0,374 in
Depth	20,5 mm
Depth	0,807 in
Strip length from	9 mm
Strip length to	11 mm
Strip length	0,39 in

Item number	Admission office	Approval no.	Voltage [V]	Current [A]	Cross section [mm²]
224-114	ABS	04-HG476172-PDA	400	24	0,5-2,5
224-114	ASTA	Cert.No.174	400	24	0,5-2,5
224-114	BBJ	B/12/694/03	400	24	2,5
224-114	BV	11914/AO	300	24	2,5
224-114	CCA	DK2527	400	24	2,5
224-114	CSA	154112-1059435	300		14-12
224-114	DEMKO	119688/01/02			2,5
224-114	DEMKO	143835-01	400	24	2,5
224-114	DNV	E7569	400	24	2,5
224-114	FIMKO	163400-01			2,5
224-114	GL	17294-00HH	300	24	2,5
224-114	KEMA	96.1739.01	400	24	2,5
224-114	LR	04/20013(E1)	400	24	2,5
224-114	NEMKO	P96191377			2,5
224-114	ÖVE	1193-032-01	400	24	0,5-2,5
224-114	ÖVE	1193-032-02	400	24	0,5-2,5
224-114	RMR	11130002	400	24	0,5-2,5
224-114	RosTesT	B09523	400	24	0,5-2,5
224-114	SEMKO	9617079			2,5
224-114	UL	E69654	300	20	18-16
224-114	VDE	95667	400	24	2,5T110

Sorting criteria: admission office - approval number

© WAGO Kontakttechnik GmbH & Co. KG

Specifications are subject to changes and errors may be expected