







注記:
1. 適合端子: 5263PBT
2. 嵌合相手: 5267 シリーズ, 5268 シリーズ
3. 9 極以上はロックなし。

	38.3	35	50-37-5153	5264-15	15
	35.8	32.5	5143	14	14
	33.3	30	5133	13	13
	30.8	27.5	5123	12	12
	28.3	25	5113	11	11
	25.8	22.5	5103	10	10
	23.3	20	5093	9	9
21.4	20.8	17.5	5083	8	8
18.9	18.3	15	5073	7	7
16.4	15.8	12.5	5063	6	6
13.9	13.3	10	5053	5	5
11.4	10.8	7.5	5043	4	4
8.9	8.3	5	5033	3	3
6.4	5.8	2.5	5023	2	2
C	B	A	EDP NO.	ENG.NO.	極数

角度	ANGLE	±3°			
30 以上	OVER	±0.3			
10 以上 30 未満	OVER UNDER	±0.25			
10 未満	UNDER	±0.2			
一般公差	GENERAL TOLERANCES				

材料	MATERIAL	66ナイロン UL94V-0
仕上げ	FINISH	
適用電線範囲	WIRE RANGE	
被覆外径	INS. RANGE	
DRAWN BY	CHK'D BY	9/17/26
K.TOJO	M.FUKUSHIMA	9/17/26
APP'D BY	DATE	9/17/26
M.ENOMOTO	SCALE	5-1

MOLEX-JAPAN CO.,LTD. 日本モレックス株式会社	
EDP. NO.	50-37-5**3
ENG. NO.	SD-5264-N
TITLE 名称	2.5 LOW PROFILE RECEPTACLE HOUSING

