




LEFT CONN.	RIGHT CONN.
SC A	ST RED
SC B	ST BLACK

NOTES:

- 1 ATTENUATION $\leq 0,3$ dB FOR BOTH CONNECTORS
MEASURED AT 1300nm ACC. TO IEC 61300-3-4
EQUILIBRIUM MODE CONDITION
- 2 INDIVIDUAL LENGTH DIFFERENCE ON SC SIDE ≤ 5 mm
- 3 INDIVIDUAL LENGTH DIFFERENCE ON ST SIDE ≤ 50 mm
- 4 SUPPLY FILLED OUT TEST RESULT SHEET WITH EACH
INDIVIDUALLY PACKED ASSEMBLY
- 5 DAT LABEL INFO:

- UNIQUE SERIAL NUMBER

- TYCO LOGO PN

- MANUFACTURING LOCN.
- 6 BLANK LABEL
- 7 CABLE INFO:

CORE DIA - 50/125 μ m

OUTER DIA - 2,5 mm

JACKET COLOR - ORANGE

JACKET MATERIAL - LSZH

STANDARD LENGTHS ACCORDING TO CUSTOMER DRAWING 1206850	
PART NUMBER	"L" (Meter)
X-5349567-Y	XY,0

2	-	DAT-85 LABEL	12
2	-	ST CONNECTOR KIT BAYONET MM	11
2	-	ST CRIMP EYELET	10
1	-	ST BOOT BLACK	9
1	-	ST BOOT RED	8
2	-	PROTECTIVE COVER, 2.5MM, BLACK	7
1	-	SC DUPLEX HOUSING. BEAM HALF	6
1	-	SC DUPLEX HOUSING, RET. PLATE HALF	5
2	-	SC CERAMIC, OVERMOLDED	4
2	-	SC CRIMP EYELET	3
2	-	FOAC BOOT 2.0 BEIGE SC/FC	2
L	-	FOCAB 50/125S 2,5TZ LSZH ORANGE	1
Qty	Part Number	Description	Item

THIS DRAWING IS A CONTROLLED DOCUMENT.

DIMENSIONS:

mm

MATERIAL

-

TOLERANCES UNLESS OTHERWISE SPECIFIED:

0 PLC ± -

1 PLC ± -

2 PLC ± -

3 PLC ± -

4 PLC ± -

ANGLES ± -

FINISH -

DWN 11 OCT 06 VINAYAK KULKARNI

CHK 11 OCT 06 R VENKATESH

APVD 11 OCT 06 R VENKATESH

PRODUCT SPEC -

APPLICATION SPEC -

WEIGHT -

CUSTOMER DRAWING

Tyco Electronics Corporation
FOBU, Bangalore, India

NAME

SIZE

A2

CAGE CODE

00779

DRAWING NO

C=5349567

RESTRICTED TO

-

SCALE

NTS

SHEET

1

OF

1

REV

A